



YNS451RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS451RT](#)



HYSPLICE™ Al Tube Jumper Loop Sleeve, For EHV, 840.2-927.2 kcmil(ACAR), 795-1000 kcmil(Al), 715.5-874.5 kcmil(ACSR), 230 kV, 10.60" L, 725 Index.

General

Connector Type	Splice
Die Index	725
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016497
UPC 12 Digit	7818100164977

Dimensions

Dimension - Diameter Max Size inch	1.80 in
Dimension - L Length Overall mm	269 mm
Dimension - Length Overall inch	10.60 in
Dimension - Outside Diameter inch	1.80 in

Conductor Related

Conductor - ACAR Str Size Range	715.5 KCMIL - 874.5 KCMIL
Conductor - ACSR Str Size	715.5 (26/7) Starling kcmil; 715.5 (30/19) Redwing kcmil; 795 (54/7) Condor kcmil
Conductor - ACSR Str Size Range	715.5 (26/7) Starling kcmil-795 (54/7) Condor kcmil
Conductor - AL Str Size	795 KCMIL - 1000 KCMIL
Conductor - AL Str Size Range	795 KCMIL - 1000 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	1008

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD058033-01](#)



A proud member of the Hubbell Family.