



YNS451RTHT, Aluminum Loop Splice

By Burndy
Catalog # [YNS451RTHT](#)



Aluminum loop Hysplice, 715.5-874.5 kcmil ACSS, 18.60 in long.

General

Connector Type	Splice
Die Index	725
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810480311

Dimensions

Dimension - L Length Overall mm	472 mm
Dimension - Length Overall inch	18.6 in
Dimension - Outside Diameter inch	1.8 in

Conductor Related

Conductor - ACSR Str Size	715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/7) Mallard;874.5 (54/7) Crane
Conductor - AL Str Size	715.5;795.5;800;874.5

Certifications and Compliance

Standards - RoHS Compliance Status CM

Logistics

Carton Quantity	6
Minimum Pack Quantity	5
Pallet Quantity	576

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10097739](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNS451RTHT-SPEC-EN | REV 8/2023