



YNS49R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS49R](#)



HYSPLICE™ Al Tube Jumper Loop Sleeve, 900 -1113 kcmil(ACAR), 1033.5-1272 kcmil(Al), 900-1113 kcmil 45/7Str(ACSR), 230 kV, 10.08" L.

General

Connector Type	Splice
Die Index	727
Material	Aluminum
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810085875
UPC 12 Digit	7818100858755

Dimensions

Dimension - L Length Overall mm	256 mm
Dimension - Length Overall inch	10.08 in
Dimension - Outside Diameter inch	1.97 in

Conductor Related

Conductor - ACAR Str Size	950 (37) kcmil;1000 (61) kcmil;1100 (61) kcmil;1200 (61) kcmil
Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACSR Str Size	900 (54/7) Canary kcmil;954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil;1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil
Conductor - ACSR Str Size Range	900 (54/7) Canary kcmil-1113 (54/19) Finch kcmil
Conductor - AL Str Size	1033.5 KCMIL - 1272 KCMIL
Conductor - AL Str Size Range	1033.5 KCMIL - 1272 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	1008

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd062800-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNS49R-SPEC-EN | REV 8/2023