



YNS49RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS49RT](#)



HYSPLICE™ Al Tube Jumper Loop Sleeve, 900 - 1113 Kcmil ACSR, 1033.5 - 1272 Kcmil Al, 983.1 - 1198 Kcmil ACAR, above 230 kV.

General

Connector Type	Splice
Die Index	727
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810016480
UPC 12 Digit	7818100164800

Dimensions

Dimension - Diameter Max Size inch	1.97 in
Dimension - L Length Overall mm	271 mm
Dimension - Length Overall inch	10.66 in
Dimension - Outside Diameter inch	1.97 in

Conductor Related

Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACSR Str Size	954 (45/7) Rail kcmil;954 (54/7) Cardinal kcmil;1033.5 (45/7) Ortolan kcmil;1033.5 (54/7) Curlew kcmil;900 (45/7) Ruddy kcmil;1113 (45/7) Bluejay kcmil
Conductor - ACSR Str Size Range	900 (45/7) Canary kcmil-1113 (45/7) Bluejay kcmil
Conductor - AL Str Size	1033.5 KCMIL - 1272 KCMIL
Conductor - AL Str Size Range	1033.5 KCMIL - 1272 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus™	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	1080

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD058033-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNS49RT-SPEC-EN | REV 8/2023