



YNS54R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS54R](#)



HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 1534 Kcmil ACAR, 1590-1600 Kcmil AL, 1431 Kcmil ACSR.

General

Connector Type	Splice
Die Index	728
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810180648
UPC 12 Digit	7818101806488

Dimensions

Dimension - L Length Overall mm	393 mm
Dimension - Length Overall inch	15.48 in
Dimension - Outside Diameter inch	2.25 in

Conductor Related

Conductor - ACAR Str Size Range	1534 KCMIL
Conductor - ACSR Str Size	1431 (54/19) Plover kcmil
Conductor - ACSR Str Size Range	1431 (54/19) Plover kcmil
Conductor - AL Str Size	1590 KCMIL - 1600 KCMIL
Conductor - AL Str Size Range	1590 KCMIL - 1600 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus™	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd062800-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNS54R-SPEC-EN | REV 8/2023