



YNS56RT, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS56RT](#)



HYSPLICE™, ACCOM: 1510.5-1590 ACSR 1700-1800 ALUM 1650 (42/19) ACAR INDEX: 729/BURNDY 204/T&B.

General

Connector Type	Splice
Die Index	729
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810098059
UPC 12 Digit	7818100980599

Dimensions

Dimension - Diameter Max Size inch	2.50 in
Dimension - L Length Overall mm	396 mm
Dimension - Length Overall inch	15.58 in
Dimension - Outside Diameter inch	2.50 in

Conductor Related

Conductor - ACAR Str Size Range	1650 KCMIL - 42/19 STR
Conductor - ACSR Cmpt Run Range	1510.5 KCMIL - 1590 KCMIL
Conductor - ACSR Str Size	1510.5 (45/7) Nuthatch kcmil;1590 (45/7) Lapwing kcmil;1590 (54/19) Falcon kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) Nuthatch kcmil-1590 (54/19) Falcon kcmil
Conductor - AL Str Size	1700 KCMIL - 1800 KCMIL
Conductor - AL Str Size Range	1700 KCMIL - 1800 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus™	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SD058033-01](#)



A proud member of the Hubbell Family.