



## YNS594R, Aluminum Jumper Loop Sleeve

By Burndy  
Catalog # [YNS594R](#)



HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 2267-2500 Kcmil ACAR, 2500 Kcmil AL, 2300 Kcmil ACSR, ?230 kV.

### General

Catalog Number	YNS594R
Connector Type	Splice
Die Index	740
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810469774
UPC 12 Digit	7818104697744

### Dimensions

Dimension - L Length Overall mm	357 mm
Dimension - Length Overall inch	14.04 in
Dimension - Outside Diameter inch	2.60 in

### Conductor Related

Conductor - ACAR Str Size Range	2267 KCMIL - 2500 KCMIL
Conductor - ACSR Str Size	2300 KCMIL
Conductor - ACSR Str Size Range	2300 KCMIL
Conductor - AL Str Size	2500 KCMIL
Conductor - AL Str Size Range	2500 KCMIL

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YNS-R\\_LINEART\\_BW](#)
- [Sales Drawings - sd062800-01](#)
- [Specifications - YNS594R](#)



A Hubbell brand