



YNS594RT, Aluminum Splice

By Burndy
Catalog # [YNS594RT](#)

HYSPLICE™, ACCOM: 2300 KCMIL ACSR 2500 KCMIL ALUM
2267 KCMIL - 2500 KCMIL ACAR USE BURNDY DIE 740
OVERLAP CRIMPS.



General

Connector Type	Splice
Die Index	740
Material	Aluminum
Trade Name	HYSPLICE™
UPC	781810180655
UPC 12 Digit	7818101806555

Dimensions

Dimension - Diameter Max Size inch	2.60 in
Dimension - L Length Overall mm	420 mm
Dimension - Length Overall inch	16.53 in
Dimension - Outside Diameter inch	2.60 in

Conductor Related

Conductor - ACAR Str Size Range	2267 KCMIL - 2500 KCMIL
Conductor - ACSR Str Size	2300 KCMIL
Conductor - ACSR Str Size Range	2300 KCMIL
Conductor - AL Str Size	2500 KCMIL
Conductor - AL Str Size Range	2500 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD058033-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNS594RT-SPEC-EN | REV 8/2023