

YNS59R, Aluminum Jumper Loop Sleeve

By Burndy
Catalog # [YNS59R](#)



HYSPLICE™, AL Tube jumper loop sleeve for ACAR and Stranded Aluminum conductor, 2250-2300 Kcmil AL, 2156-2167 Kcmil ACSR, 230 kV.

General

Catalog Number	YNS59R
Connector Type	Splice
Die Index	735
Material	Aluminum
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810180662
UPC 12 Digit	7818101806622

Dimensions

Dimension - L Length Overall mm	370 mm
Dimension - Length Overall inch	14.56 in
Dimension - Outside Diameter inch	2.50 in

Conductor Related

Conductor - ACSR Str Size	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	2156 (84/19) Bluebird kcmil;2167 (72/7) Kiwi kcmil
Conductor - AL Str Size	2250 - 2300 KCMIL
Conductor - AL Str Size Range	2250 - 2300 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YNS-R_LINEART_BW](#)
- [Sales Drawings - sd062800-01](#)
- [Specifications - YNS59R](#)