



# YNT451R451R, Aluminum 2-piece T-Tap Connector, 2-hole

By Burndy  
Catalog # [YNT451R451R](#)



Aluminum Compression Two piece T-Tap connector, 230 kV, #4 AWG ACAR, 795-1000 kcmil Aluminum, 2 Pad holes.

## General

Connector Type	Tap
Die Index	725
Material	Aluminum
UPC	781810095157
UPC 12 Digit	7818100951577

## Dimensions

Dimension - B Length inch	4.56 in
Dimension - Height fraction	7-1/2 in
Dimension - Height inch	7.7 in
Dimension - Length Overall inch	17.6 in

## Conductor Related

Conductor - ACAR Str Size	840.2 - 927.2
Conductor - ACAR Str Size Range	840.2 - 927.2
Conductor - ACAR Str Tap	850 (37) kcmil;900 (37) kcmil
Conductor - ACAR Str Tap Range	850 (37) kcmil-900 (37) kcmil
Conductor - ACSR Str Size	715.5 (26/7) kcmil;715.5 (30/19) kcmil;795 (54/7) kcmil
Conductor - ACSR Str Size Range	715.5 (26/7) kcmil-795 (54/7) kcmil
Conductor - ACSR Str Tap	715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil;874.5 (54/7) Crane kcmil
Conductor - ACSR Str Tap Range	715.5 (54/7) Crow kcmil-874.5 (54/7) Crane kcmil

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - YNT451R451R\\_MODEL-STEP](#)
- [3D Models - YNT451R451R\\_MODEL-PDF](#)
- [3D Models - YNT451R451R\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR\\_YNT-R-R\\_LINEART\\_BW](#)



A proud member of the Hubbell Family.