



# YNT49R49R, Aluminum 2-Piece T-Tap Connector, 2-hole

By Burndy  
Catalog # [YNT49R49R](#)



Aluminum Compression Two piece T-Tap connector, 230 kV, 1033.5-1272 kcmil Aluminum, 2 Pad holes.

## General

Connector Type	Tap
Die Index	727
Material	Aluminum
UPC	781810116562
UPC 12 Digit	7818101165622

## Dimensions

Dimension - Height fraction	7-3/4 in
Dimension - Height inch	7.75
Dimension - Length Overall inch	17.50

## Electrical Ratings

Voltage Rating	230 kV
----------------	--------

## Conductor Related

Conductor - ACAR Str Run Range	983.1 kcmil -1198 kcmil
Conductor - ACAR Str Tap Range	983.1 kcmil -1198 kcmil
Conductor - ACSR Str Run Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - ACSR Str Tap Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - AL Str Run Range	1033.5 kcmil-1272 kcmil
Conductor - AL Str Tap Range	1033.5 kcmil-1272 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNT49R49R-SPEC-EN | REV 8/2023