



YNT49R49RHT, Aluminum 2-Piece T-Tap Connector, 2-hole

By Burndy
Catalog # [YNT49R49RHT](#)



Aluminum Compression Two piece T-Tap connector, 230 kV, 1033.5-1272 kcmil Aluminum, 2 Pad holes.

General

Connector Type	Tap
Die Index	L727
UPC	781810488027
UPC 12 Digit	7818104880277

Dimensions

Dimension - Height inch	10.54
Dimension - Length Overall inch	25.66 in

Electrical Ratings

Voltage Rating	230 kV
----------------	--------

Conductor Related

Conductor - ACSR Str Run Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - ACSR Str Tap Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - ACSS Str Size Range	900 (45/7) kcmil-1113 (45/7) kcmil
Conductor - AL Str Run Range	1033.5 kcmil-1272 kcmil
Conductor - AL Str Tap Range	1033.5 kcmil-1272 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets



A proud member of the Hubbell Family.