



# YNU43R, Aluminum Repair Sleeve

By Burndy  
Catalog # [YNU43R](#)

Al Repair Sleeve, 605 - 666.6 kcmil ACSR, 700 - 800 kcmil Al,  
16.00" L, 724 Index.



## General

Connector Type	Splice
Die Index	724
Material	Aluminum
UPC	781810016527
UPC 12 Digit	7818100165277

## Dimensions

Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16.00 in
Dimension - Outside Diameter inch	1.61 in

## Conductor Related

Conductor - ACSR Str Size	605 (24/7) kcmil;605 (26/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;666.6 (24/7) kcmil
Conductor - ACSR Str Size Range	605 (24/7) kcmil-666.6 (24/7) kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD065207-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YNU43R-SPEC-EN | REV 8/2023