



YNU56R, Aluminum Repair Sleeve

By Burndy
Catalog # [YNU56R](#)

Al Repair sleeve, HV and EHV applications, 1510.5 - 1590 Kcmil ACSR, 19 IN L, 729 Index, For temporary restoration of conductivity to damaged ACSR Transmission Lines.



General

Connector Type	Splice
Die Index	729
Material	Aluminum
UPC	781810129357
UPC 12 Digit	7818101293577

Dimensions

Dimension - L Length Overall mm	483 mm
Dimension - Length Overall inch	19.00 in
Dimension - Outside Diameter inch	2.5 in

Conductor Related

Conductor - ACSR Str Size	1510.5 (45/7) kcmil;1510.5 (54/19) Kcmil;1590 (45/7) kcmil;1590 (54/19) kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) kcmil-1590 (54/19) kcmil
Conductor - AL Str Size	1700 kcmil;1750 kcmil;1800 kcmil
Conductor - AL Str Size Range	1700 kcmil-1800 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD065207-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YNU56R-SPEC-EN | REV 8/2023