



YNU59RHT, Repair Sleeve for ACSS Conductor

By Burndy
Catalog # [YNU59RHT](#)



Repair Sleeve for ACSS Conductor.

General

Connector Type	Splice
Die Index	735
UPC	621945468696
UPC 12 Digit	781810515358

Dimensions

Dimension - L Length Overall mm	686 mm
Dimension - Length Overall inch	27.00 in

Conductor Related

Conductor - ACSS Str Size	2156 (84/19) kcmil;2167 (72/7) kcmil
Conductor - ACSS Str Size Range	2156 (84/19) kcmil-2167 (72/7) kcmil

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	8
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50025987](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YNU59RHT-SPEC-EN | REV 5/2024