



## YOT3434, Copper T-Tap Connector, 2-piece design

By Burndy  
Catalog # [YOT3434](#)



Cast copper T-tap connector with two-piece line element and tubular tap for joining hard and medium drawn copper. Design simplifies installation on large conductors.

### General

Connector Type	Tap
Die Index	210
Die Index Run Side	210
Die Index Tap Side	210
Material	Copper
UPC	781810014714

### Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - Height fraction	4-8/10
Dimension - Height inch	4.82 in
Dimension - L Length Overall mm	264 mm
Dimension - Length BB inch	2.5 in
Dimension - Length Overall inch	10.38 in
Dimension - Outside Diameter inch	1.4 in
Dimension - Width fraction	1-23/25 in
Dimension - Width inch	1.92 in
Dimension - Width mm	49 mm

### Conductor Related

Conductor - Copper Str Run	500 kcmil
Conductor - Copper Str Run Range	500 kcmil
Conductor - Copper Str Tap	500 kcmil
Conductor - Copper Str Tap Range	500 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	2
-----------------------	---

### Product Assets

[Sales Drawings - SD024930-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YOT3434-SPEC-EN | REV 8/2023