



# YOU32R, Aluminum Repair Sleeve

By Burndy  
Catalog # [YOU32R](#)

Cast Aluminium Repair Sleeve, 300 (26-7) kcmil, 13 IN L, 316 Index.



## General

Connector Type	Splice
Die Index	316
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810016046
UPC 12 Digit	7818100160466

## Dimensions

Dimension - L Length Overall mm	329 mm
Dimension - Length Overall inch	12.94 in

## Conductor Related

Conductor - ACSR Str Size	300.0 (26/7) Ostrich kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil
Conductor - AL Str Size	300 kcmil
Conductor - AL Str Size Range	300 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	6
-----------------------	---

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD021894](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YOU32R-SPEC-EN | REV 8/2023