

YP28C28, Figure 6-shaped Copper Tap Connector

By Burndy
Catalog # [YP28C28](#)



Figure 6 - shaped, wide range-taking CU compression tap connector for primary service taps and secondary service drops, Width: 1.00.

Features

- Compression tap connector for primary service taps and secondary service drops
- Connector can be gripped in tool and slipped over the line for easy installation

Application

For Extra Wide Range Of Copper And Primary Service Taps And Secondary Service Drops

General

Catalog Number	YP28C28
Connector Type	Tap
Die Index	D
EU RoHS Indicator	Yes
Material	Copper
Plated	Y
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YP-C
UPC	781810117958
UPC 12 Digit	7818101179588

Dimensions

Dimension - D inch	1.00 in
Dimension - Height inch	2.06 in
Dimension - Height mm	52 mm
Dimension - L Length Overall mm	25 mm

Conductor Related

Conductor - Copper Str Run	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Tap	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG-4/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YP-C_LineArt](#)
[Sales Drawings - SC058072-01](#)
[Specifications - YP28C28](#)