



YP28U2, Figure 3-shaped Aluminum Connector with adjustable spacer

By Burndy

Catalog # [YP28U2](#)

Wide range, universal and reversible, Figure 3 shaped aluminum connector with adjustable overhanging spacer that separates conductors, Conductor Groove A Stranded: 4/0.



Features

- Wide range universal and reversible, Figure 3-shaped aluminum connector features adjustable overhanging spacer that separates conductors
- Spacer holds run or tap in place, permitting lineman to either approach the line ready to crimp or to assemble connector and tap on run and then crimp
- Massive aluminum design minimizes conductor corrosion due to galvanic action
- Pre-filled with PENETROX joint compoud and stripsealed

Application

For Copper, Aluminum Or ACSR Conductors

General

Catalog Number	YP28U2
Die Index	D3
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	CABELOK CRIMPIT
Trade Name	CABELOK™ CRIMPIT™
Type	YP-U
UPC	781810134986
UPC 14 Digit GTIN	00781810134986

Dimensions

Dimension - Height inch	1.70 in
Dimension - Length Overall inch	3.47 in
Dimension - Width inch	0.97 in

Conductor Related

Conductor - ACSR Str Size A	3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size A Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG

Conductor - ACSR Str Size B	4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size A	3/0 AWG;4/0 AWG
Conductor - AL Str Size A Range	3/0 AWG-4/0 AWG
Conductor - AL Str Size B	4 AWG;3 AWG;2 AWG
Conductor - AL Str Size B Range	4 AWG-2 AWG
Conductor - Copper Solid Size B	2 AWG;1 AWG;1/0 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	4 AWG;3 AWG;2 AWG;1 AWG
Conductor - Copper Str Size B Range	4 AWG-1 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - YP28U2_MODEL-IGES](#)
[3D Models - YP28U2_MODEL-PDF](#)
[3D Models - YP28U2_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YPU_Lineart](#)
[Sales Drawings - sd045569-01](#)
[Specifications - YP28U2](#)