



YPC28U28, Figure 6-shaped Connector

By Burndy
Catalog # [YPC28U28](#)



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu: 3/0 - 4/0 Str. 4/0 Sol. & 4/0, 250, 266.8 Alum. Compressed.

Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors

General

Die Index	D3
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-U
UPC	781810136683
UPC 12 Digit	7818101366833

Dimensions

Dimension - Height inch	2.75 in
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.98 in

Conductor Related

Conductor - ACSR Str Run	3/0 AWG, 4/0 AWG
Conductor - ACSR Str Run Range	3/0 AWG-4/0 AWG
Conductor - ACSR Str Tap	2/0 AWG, 3/0 AWG, 4/0 AWG
Conductor - ACSR Str Tap Range	2/0 AWG-4/0 AWG
Conductor - AL Str Run	3/0 AWG, 4/0 AWG
Conductor - AL Str Run Range	3/0 AWG-4/0 AWG
Conductor - AL Str Tap	2/0 AWG; 3/0 AWG; 4/0 AWG
Conductor - AL Str Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Run	3/0 AWG; 4/0 AWG
Conductor - Copper Str Run Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Tap	2/0 AWG; 3/0 AWG; 4/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• CU C Solid-Run• ACSR C Str-Run• AL C Str-Tap• CU C Str-Tap• CU C Solid-Tap• ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sd042248-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YPC28U28-SPEC-EN | REV 8/2023