

YPC28U4, Figure 6-shaped Connector

By Burndy
Catalog # [YPC28U4](#)



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu: 3/0 - 4/0 Str. & 4/0 - 250, 266.8 Alum. Compressed.

Application

Connector can be gripped in tool and slipped over line for easy installation. Pre-filled with PENETROX joint compound and Stripsealed to limit oxide growth and to increase the life of the connection

General

Construction Material - Main	Aluminum
Die Index	D3
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-U
UPC	781810135990
UPC 12 Digit	7818101359900

Dimensions

Dimension - Height inch	1.70 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in

Conductor Related

Conductor - ACSR Str Run	3/0 AWG, 4/0 AWG
Conductor - ACSR Str Run Range	3/0 AWG-4/0 AWG
Conductor - ACSR Str Tap	6 AWG, 5 AWG, 4 AWG
Conductor - ACSR Str Tap Range	6 AWG-4 AWG
Conductor - AL Str Run	3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	3/0 AWG-4/0 AWG
Conductor - AL Str Tap	6 AWG, 5 AWG, 4 AWG
Conductor - AL Str Tap Range	6 AWG- 4 AWG
Conductor - Copper Str Run	3/0 AWG;4/0 AWG
Conductor - Copper Str Run Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Tap	6 AWG, 5 AWG, 4 AWG
Conductor - Copper Str Tap Range	6 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - sd042248-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YPC28U4-SPEC-EN | REV 8/2023