



# YPC36A32, Figure 6-shaped Connector

By Burndy  
Catalog # [YPC36A32](#)



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:336.5 (26-7) - 556.5 (18-1).

### General

Die Index	Z
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
UPC	781810138557
UPC 12 Digit	7818101385577

### Dimensions

Dimension - Height inch	3.70 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in
Dimension - Width inch	2.00 in

### Conductor Related

Conductor - ACSR Str Run Range	336.4 kcmil-556.5 kcmil
Conductor - ACSR Str Tap Range	2/0 AWG- 397.5 kcmil
Conductor - AL Str Run	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Run Range	397 kcmil-600 kcmil
Conductor - AL Str Tap	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Tap Range	2/0 AWG-400 kcmil
Conductor - Copper Str Run	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - Copper Str Run Range	397 kcmil-600 kcmil
Conductor - Copper Str Tap	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Tap Range	2/0 AWG-400 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• CU C Solid-Run</li> <li>• ACSR C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> <li>• CU C Solid-Tap</li> <li>• ACSR C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YPC36A32-SPEC-EN | REV 8/2023