



YPC38R26U, Figure 6-shaped Connector

By Burndy
Catalog # YPC38R26U



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu:477 (19) - 600 (61).

Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors

General

Die Index	N
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-U
UPC	781810138502
UPC 12 Digit	7818101385022

Dimensions

Dimension - Height inch	2.28 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.125 in
Dimension - Width inch	1.31 in

Conductor Related

Conductor - ACSR Str Run Range	397.5 kcmil-556.5 kcmil
Conductor - ACSR Str Tap Range	1/0 AWG- 6 AWG
Conductor - AL Str Run	477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Run Range	477 kcmil-600 kcmil
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Tap Range	6 AWG-2/0 AWG
Conductor - Copper Str Run	477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - Copper Str Run Range	477 kcmil-600 kcmil
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Str Tap Range	6 AWG-2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - YPC38R26U_MODEL-STEP](#)
- [3D Models - YPC38R26U_MODEL-PDF](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YPC38R26U-SPEC-EN | REV 5/2024