



YPC40A32, Figure 6-shaped Connector

By Burndy
Catalog # [YPC40A32](#)



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:556.6 (18-1) - 795 (26-7).

General

Die Index	T
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
UPC	781810138656
UPC 12 Digit	7818101386566

Dimensions

Dimension - Height inch	3.74 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in
Dimension - Width inch	1.88 in

Conductor Related

Conductor - ACSR Str Run Range	556.5 kcmil-795 kcmil
Conductor - ACSR Str Tap Range	2/0 AWG-397.5 kcmil
Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Run Range	600 kcmil-800 kcmil
Conductor - AL Str Tap	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Tap Range	2/0 AWG-400 kcmil
Conductor - Copper Str Run	600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Run Range	600 kcmil-800 kcmil
Conductor - Copper Str Tap	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Tap Range	2/0 AWG-400 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YPC40A32-SPEC-EN | REV 8/2023