

YPC40A40, Figure 6-shaped Connector

By Burndy
Catalog # [YPC40A40](#)



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors.

General

Die Index	T
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
UPC	781810138755
UPC 12 Digit	7818101387555

Dimensions

Dimension - Height inch	3.74 in
Dimension - L Length Overall mm	97 mm
Dimension - Length Overall inch	3.84 in
Dimension - Width inch	1.88 in

Conductor Related

Conductor - ACSR Str Run Range	556.5 kcmil-795 kcmil
Conductor - ACSR Str Tap Range	556.5 kcmil-795 kcmil
Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil
Conductor - AL Str Run Range	600 kcmil-954 kcmil
Conductor - AL Str Tap	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil
Conductor - AL Str Tap Range	600 kcmil-954 kcmil
Conductor - Copper Str Run	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil
Conductor - Copper Str Run Range	600 kcmil-954 kcmil
Conductor - Copper Str Tap	600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil;954 kcmil
Conductor - Copper Str Tap Range	600 kcmil-954 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)

[Sales Drawings - sd051577-01](#)



A proud member of the Hubbell Family.