



YQE91, Nylon Pigtail Splice For 4,205 cmils

By Burndy
Catalog # [YQE91](#)

Nylon Pigtail Splice For 4,205 cmils.



Application

For Splicing A Wide Range Of Different Cable Sizes

General

Catalog Number	YQE91
Connector Type	Pigtail
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Copper
Plated	N
Plating Type	Tin
Sub Brand	INSULINK
Trade Name	INSULINK™
Type	YQE
UPC	781810029480
UPC 12 Digit	7818100294800

Dimensions

Dimension - B Length fraction	3/10 in
Dimension - B Length inch	0.30 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.76 in
Dimension - Pad Width inch	0.24 in
Dimension - Strip Length inch	5/16

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	18 AWG;17 AWG;16 AWG;15 AWG;14 AWG
Conductor - Copper Solid Size Range	18 AWG-14 AWG
Conductor - Copper Str Size	18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	18 AWG-14 AWG
Conductor Size	4,205 cmils
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

- [3D Models - YQE91_MODEL-IGES](#)
- [3D Models - YQE91_MODEL-PDF](#)
- [3D Models - YQE91_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YQE_LineArt](#)
- [Sales Drawings - sc035090-01](#)



A Hubbell brand