



YRA26UJ38, Aluminum Terminal, 1-hole

By Burndy
Catalog # [YRA26UJ38](#)



Al Compression Terminal, 1 Hole, 2/0 AWG ACSR, 2/0 Str Al/Cu, 0.41" Hole Dia.

General

Catalog Number	YRA26UJ38
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810212172
UPC 12 Digit	7818102121722

Dimensions

Dimension - B Length inch	1.43 in
Dimension - D inch	1.28 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.19 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.91 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	1 1/2 in
Thickness - Pad	0.25 in

Conductor Related

Conductor - ACSR Str Size	2/0 AWG
Conductor - AL Str Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	12000

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd077273-01](#)
- [Specifications - YRA26UJ38](#)



A Hubbell brand