



YRB2525T, Copper HYREDUCER Splice

By Burndy
Catalog # [YRB2525T](#)



Copper HYREDUCER™; 2.63 in L; 1/0 AWG (Barrel A); 1/0 AWG (Barrel B).

General

Color Code	Pink
Die Index	12;348
Material	Copper
Trade Name	HYREDUCER™
UPC	781810367797
UPC 12 Digit	7818103677977

Dimensions

Dimension - B Length inch	0.98 in
Dimension - Length Overall inch	2.63 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Strip Length inch	1-1/16 in

Conductor Related

Conductor - Copper Str Size A 1/0 AWG
Conductor - Copper Str Size B 1/0 AWG

Certifications And Compliance

Standards - RoHS Compliance CM
Status

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YRBT_HYREDUCER_FIG1_LineArt](#)
[Sales Drawings - SE211538-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YRB2525T-SPEC-EN | REV 5/2024