



YRB2525TW, Copper - Compression Reducer

By Burndy
Catalog # [YRB2525TW](#)



Cu Splice, 1/0(Cu)(Barrel A & B), 35 kV, 2.63" L, Hot Tin Dipped Plating, Pink, 12 or 348 Index, For Cu to Cu.

General

Color Code	Pink
Die Index	12;348
Material	Copper
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192825
UPC 12 Digit	7818101928255

Dimensions

Dimension - B Length inch	0.98 in
Dimension - Length Overall inch	2.63 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Strip Length inch	1-1/16 in

Conductor Related

Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	19200

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE211538-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YRB2525TW-SPEC-EN | REV 8/2023