



YRB25U2TTN, Aluminum HYREDUCER Splice

By Burndy
Catalog # [YRB25U2TTN](#)



Aluminum HYREDUCER™; 3.25 in L; Tin Plated; 1/0 (19 STR)
AWG (Barrel A); #2 (7 STR) AWG (Barrel B).

General

Catalog Number	YRB25U2TTN
Color Code	Orange; Tan
Connector Type	Reducer
Die Index	14;296
Material	Aluminum
Plating Type	Tin
Trade Name	HYREDUCER™
UPC	781810246818
UPC 12 Digit	7818102468188

Dimensions

Dimension - B Length inch	1.35 in
Dimension - Length Overall inch	3.25 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Strip Length inch	1-7/16 in

Conductor Related

Conductor - AL Str Size A	1/0 (19 STR) AWG
Conductor - AL Str Size B	#2 (7 STR) AWG
Conductor - Copper Str Size A	1/0 (19 STR) AWG
Conductor - Copper Str Size B	#2 (7 STR) AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section K - Underground](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..211534-01](#)
[Specifications - YRB25U2TTN](#)



A Hubbell brand