



## YRB27U25TW, Aluminum HYREDUCER Splice

By Burndy  
Catalog # [YRB27U25TW](#)



Al HYREDUCER™ Splice, 3.69" L, 3/0 (19 STR) AWG (Al/Cu)  
(Barrel A), 1/0 (19 STR) AWG (Al/Cu)(Barrel B), White, 298  
Index, For Al to Al&Al to Cu.

### General

Catalog Number	YRB27U25TW
Color Code	White
Connector Type	Reducer
Die Index	298
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810209059
UPC 12 Digit	7818102090599

### Dimensions

Dimension - B Length inch	1.53 in
Dimension - Length Overall inch	3.69 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Strip Length inch	1-5/8 in

### Conductor Related

Conductor - AL Str Size A	3/0 (19 STR) AWG
Conductor - AL Str Size B	1/0 (19 STR) AWG
Conductor - Copper Str Size A	3/0 (19 STR) AWG
Conductor - Copper Str Size B	1/0 (19 STR) AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	13
Minimum Pack Quantity	1
Pallet Quantity	6032

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section K - Underground](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SE211534-02](#)  
[Specifications - YRB27U25TW](#)



A Hubbell brand