



YRB27U25TW, Aluminum HYREDUCER Splice



By Burndy
Catalog # [YRB27U25TW](#)

Al HYREDUCER™ Splice, 3.69" L, 3/0 (19 STR) AWG (Al/Cu)
(Barrel A), 1/0 (19 STR) AWG (Al/Cu)(Barrel B), White, 298
Index, For Al to Al&Al to Cu.

General

Catalog Number	YRB27U25TW
Color Code	White
Connector Type	Reducer
Die Index	298
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810209059
UPC 12 Digit	7818102090599

Dimensions

Dimension - B Length inch	1.53 in
Dimension - Length Overall inch	3.69 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Strip Length inch	1-5/8 in

Conductor Related

Conductor - AL Str Size A	3/0 (19 STR) AWG
Conductor - AL Str Size B	1/0 (19 STR) AWG
Conductor - Copper Str Size A	3/0 (19 STR) AWG

Conductor - Copper Str Size B 1/0 (19 STR) AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	13
Minimum Pack Quantity	1
Pallet Quantity	6032

Product Assets

- [Catalogs - BURNDY Master Catalog - Section K - Underground](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211534-02](#)
- [Specifications - YRB27U25TW](#)