



YRB2825TW, Copper - Compression Reducer

By Burndy
Catalog # [YRB2825TW](#)



Copper Hyreducer; 2.84 in L; Hot Tin Dipped; 4/0 (.528) (Barrel A); 1/0 (.372) (Barrel B).

General

Catalog Number	YRB2825TW
Color Code	Purple
Die Index	15
Material	Copper
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192832
UPC 12 Digit	7818101928322

Dimensions

Dimension - B Length inch	1.16 in
Dimension - Length Overall inch	2.84 in
Dimension - Outside Diameter inch	0.69 in

Conductor Related

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	7200

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211538-01](#)
- [Specifications - YRB2825TW](#)