



YRB2828T, Copper - Compression Reducer

By Burndy
Catalog # [YRB2828T](#)



Copper HYREDUCER™; 2.84 in L; Hot Tin Dipped; 4/0 (.528) (Barrel A); 4/0 (.528) (Barrel B).

General

Catalog Number	YRB2828T
Color Code	Purple
Die Index	15
Material	Copper
Trade Name	HYREDUCER™
UPC	781810367827
UPC 12 Digit	7818103678277

Dimensions

Dimension - B Length inch	1.16 in
Dimension - Length Overall inch	2.84 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Strip Length inch	1-7/32 in

Conductor Related

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	14400

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YRBT_HYREDUCER_FIG2_LineArt](#)
- [Sales Drawings - SE211538-01](#)
- [Specifications - YRB2828T](#)



A Hubbell brand