



YRB28U2TW, Aluminum HYREDUCER Splice

By Burndy
Catalog # [YRB28U2TW](#)



Al HYREDUCER™ Splice, 3.69" L, 4/0 (19 STR) AWG (Al/Cu) (Barrel A), #2 (7 STR) AWG (Al/Cu)(Barrel B), White, 298 Index, For Al to Al&Al to Cu.

General

Color Code	White
Connector Type	Reducer
Die Index	298
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810209073
UPC 12 Digit	7818102090733

Dimensions

Dimension - B Length inch	1.53 in
Dimension - Length Overall inch	3.69 in
Dimension - Outside Diameter inch	0.85 in
Dimension - Strip Length inch	1-5/8 in

Conductor Related

Conductor - AL Str Size A	4/0 (19 STR) AWG
Conductor - AL Str Size B	#2 (7 STR) AWG
Conductor - Copper Str Size A	4/0 (19 STR) AWG
Conductor - Copper Str Size B	#2 (7 STR) AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	11600

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE211534-02](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YRB28U2TW-SPEC-EN | REV 8/2023