



## YRB3131TW, Copper - Compression Reducer

By Burndy  
Catalog # [YRB3131TW](#)



Cu Splice, 350 kcmil(Cu)(Barrel A & B), 35 kV, 3.34" L, Hot Tin Dipped Plating, Red, 18 or 324 Index, For Cu to Cu.

### General

Catalog Number	YRB3131TW
Color Code	Red
Die Index	18;324
Material	Copper
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192863

### Dimensions

Dimension - B Length inch	1.36 in
Dimension - Length BB inch	1.36 in
Dimension - Length Overall inch	3.34 in
Dimension - Outside Diameter inch	0.88 in

### Conductor Related

Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size B	350 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	40
Minimum Pack Quantity	1
Pallet Quantity	7400

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211538-01](#)
- [Specifications - YRB3131TW](#)