



YRB322CTTN, Copper HYREDUCER Splice, Tin Plated

By Burndy
Catalog # [YRB322CTTN](#)



HYREDUCER™, Tin plated, 3.48 in long.

General

Catalog Number	YRB322CTTN
Color Code	Blue
Die Index	19;470
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	HYREDUCER™
UPC	781810439463

Dimensions

Dimension - B Length inch	1.38 in
Dimension - Length BB inch	1.38 in
Dimension - Length Overall inch	3.48 in
Dimension - Outside Diameter inch	0.95 in

Conductor Related

Conductor - Copper Str Size A	400 kcmil
Conductor - Copper Str Size B	2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	3700

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211538-01](#)
- [Specifications - YRB322CTTN](#)



A Hubbell brand