



## YRB3328TTN, Copper HYREDUCER Splice, Tin Plated

By Burndy  
Catalog # [YRB3328TTN](#)



HYREDUCER™, Tin plated, 3.57 in long.

### General

Catalog Number	YRB3328TTN
Color Code	Gray
Die Index	326;538
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	HYREDUCER™
UPC	781810439470

### Dimensions

Dimension - B Length inch	1.45 in
Dimension - Length BB inch	1.45 in
Dimension - Length Overall inch	3.57 in
Dimension - Outside Diameter inch	1.01 in

### Conductor Related

Conductor - Copper Str Size A	450 kcmil
Conductor - Copper Str Size B	4/0 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	7400

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211538-01](#)
- [Specifications - YRB3328TTN](#)



A Hubbell brand