



YRB34U25TW, Aluminum HYREDUCER Splice, Tin Plated

By Burndy
Catalog # [YRB34U25TW](#)



HYREDUCER™, Hot tin dipped, 6.00" long.

General

Color Code	Pink
Connector Type	Reducer
Die Index	300
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810209110

Dimensions

Dimension - B Length fraction	2-7/10 in
Dimension - B Length inch	2.70 in
Dimension - Length Overall inch	6.00 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Strip Length inch	2-13/16 in

Conductor Related

Conductor - AL Str Size A	500 kcmil
Conductor - AL Str Size B	1/0 AWG
Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE211534-04_D](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YRB34U25TW-SPEC-EN | REV 8/2023