



YRB34U31TW, Aluminum - Compression Reducer

By Burndy
Catalog # YRB34U31TW



Al Hyreducer Splice, 6.00" L, 500 kcmil(Al/Cu)(Barrel A), 350 kcmil(Al/Cu)(Barrel B), Hot Tin Dipped Plating, Pink, 300 Index, For Al to Al&Al to Cu.

General

Catalog Number	YRB34U31TW
Color Code	Pink
Connector Type	Reducer
Die Index	300
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192733

Dimensions

Dimension - B Length fraction	2-7/10 in
Dimension - B Length inch	2.70 in
Dimension - Length Overall inch	6.00 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Strip Length inch	2-13/16 in

Conductor Related

Conductor - AL Str Size A	500 kcmil
Conductor - AL Str Size B	350 kcmil
Conductor - Copper Str Size A	500 kcmil
Conductor - Copper Str Size B	350 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2400

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section K - Underground](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211534-04_D](#)
- [Specifications - YRB34U31TW](#)