



## YRB3939TW, Copper - Compression Reducer

By Burndy  
Catalog # [YRB3939TW](#)



Cu Splice, 750 kcmil(Cu)(Barrel A & B), 35 kV, 4.75" L, Hot Tin Dipped Plating, Black, 24 Index, For Cu to Cu.

### General

Catalog Number	YRB3939TW
Color Code	Black
Die Index	24
Material	Copper
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192917

### Dimensions

Dimension - B Length inch	2.06 in
Dimension - Length BB inch	2.06 in
Dimension - Length Overall inch	4.75 in
Dimension - Outside Diameter inch	1.30 in

### Conductor Related

Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	750 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	2220

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211538-01](#)
- [Specifications - YRB3939TW](#)