



YRB39U28TW, Aluminum HYREDUCER Splice, Tin Plated

By Burndy
Catalog # [YRB39U28TW](#)



HYREDUCER™, 750 kcmil, 6.74" L.

General

Catalog Number	YRB39U28TW
Color Code	Yellow
Connector Type	Reducer
Die Index	936
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810282694

Dimensions

Dimension - B Length inch	2.87 in
Dimension - Length Overall inch	6.74 in
Dimension - Outside Diameter inch	1.46 in
Dimension - Strip Length inch	3 in

Conductor Related

Conductor - AL Str Size A	750 kcmil;700 kcmil
Conductor - AL Str Size B	4/0 AWG
Conductor - Copper Str Size A	750 kcmil;700 kcmil
Conductor - Copper Str Size B	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2400

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE..211534-05](#)
- [Specifications - YRB39U28TW](#)



A Hubbell brand