



YRB39U34TW, Aluminum - Compression Reducer

By Burndy
Catalog # YRB39U34TW



Hyreducer Splice; 750 kcmil 61 Str or 750 kcmil Compct (.908 Dia.) 61 Str (Barrel A); 500 kcmil 37 Str or 500 kcmil Compct 19 Str Al; 37 Str. Al&Cu (Barrel B).

General

Catalog Number	YRB39U34TW
Color Code	Yellow
Connector Type	Reducer
Die Index	936
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192764

Dimensions

Dimension - B Length fraction	2-87/100 in
Dimension - B Length inch	2.87 in
Dimension - Length Overall inch	6.74 in
Dimension - Outside Diameter inch	1.46 in
Dimension - Strip Length inch	3

Conductor Related

Conductor - AL Str Size A	750 kcmil
Conductor - AL Str Size B	500 kcmil
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	500 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2400

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section K - Underground](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE..211534-05](#)
- [Specifications - YRB39U34TW](#)