



# YRB39U39TW, Aluminum - Compression Reducer

By Burndy  
Catalog # [YRB39U39TW](#)



Al Hyreducer Splice, 6.74" L, 750 kcmil(Al/Cu)(Barrel A), 750 kcmil(Al/Cu)(Barrel B), Hot Tin Dipped Plating, Yellow, 936 Index, For Al to Al&Al to Cu.

## General

Color Code	Yellow
Connector Type	Reducer
Die Index	936
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192771

## Dimensions

Dimension - B Length fraction	2-87/100 in
Dimension - B Length inch	2.87 in
Dimension - Length Overall inch	6.74 in
Dimension - Outside Diameter inch	1.46 in
Dimension - Strip Length inch	3

## Conductor Related

Conductor - AL Str Size A	750 kcmil
Conductor - AL Str Size B	750 kcmil
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size B	750 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	2400

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE..211534-05](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YRB39U39TW-SPEC-EN | REV 8/2023