



## YRB4434TW, Copper - Compression Reducer

By Burndy  
Catalog # [YRB4434TW](#)



Copper Hyreducer; 5.86 in L; Hot Tin Dipped; 1000 kcmil (1.152) (Barrel A); 500 kcmil (.813) (Barrel B).

### General

Catalog Number	YRB4434TW
Material	Copper
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810365199

### Dimensions

Dimension - B Length inch	2.50 in
Dimension - Length BB inch	2.50 in
Dimension - Length Overall inch	5.86 in
Dimension - Outside Diameter inch	1.50 in

### Conductor Related

Conductor - Copper Str Size A	1000 kcmil
Conductor - Copper Str Size B	500 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	555

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211538-01](#)
- [Specifications - YRB4434TW](#)



A Hubbell brand