



YRB44U31TW, Aluminum - Compression Reducer

By Burndy
Catalog # [YRB44U31TW](#)



Hyreducer Splice; 1000 kcmil (1.152 Dia.) 61 Str. (Barrel A); 350 kcmil 37 Str. or 350 kcmil Compact 19 Str. Al; 37 Str. Al & Cu (Barrel B).

General

Color Code	Yellow
Connector Type	Reducer
Die Index	936
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192788

Dimensions

Dimension - B Length fraction	2-87/100 in
Dimension - B Length inch	2.87 in
Dimension - Length Overall inch	6.74 in
Dimension - Outside Diameter inch	1.46 in
Dimension - Strip Length inch	3

Conductor Related

Conductor - AL Str Size A	1000 kcmil
Conductor - AL Str Size B	350 kcmil
Conductor - Copper Str Size A	1000 kcmil
Conductor - Copper Str Size B	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	1200

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE..211534-05](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YRB44U31TW-SPEC-EN | REV 8/2023