



YRB44U39TW, Aluminum - Compression Reducer

By Burndy
Catalog # YRB44U39TW



Al Hyreducer Splice, 6.74" L, 1000 kcmil(Al/Cu)(Barrel A), 750 kcmil(Al/Cu)(Barrel B), Hot Tin Dipped Plating, Yellow, 936 Index, For Al to Al&Al to Cu.

General

Catalog Number	YRB44U39TW
Color Code	Yellow
Connector Type	Reducer
Die Index	936
Material	Aluminum
Plating Type	Tin - Hot Dipped
Trade Name	HYREDUCER™
UPC	781810192801

Dimensions

Dimension - B Length fraction	2-87/100 in
Dimension - B Length inch	2.87 in
Dimension - Length Overall inch	6.74 in
Dimension - Outside Diameter inch	1.46 in

Conductor Related

Conductor - AL Str Size A	1000 kcmil
Conductor - AL Str Size B	750 kcmil;700 kcmil
Conductor - Copper Str Size A	1000 kcmil
Conductor - Copper Str Size B	750 kcmil;700 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	1200

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section K - Underground](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211534-05](#)
- [Specifications - YRB44U39TW](#)