



## YRB6C6CTTN, Copper - Compression Reducer

By Burndy  
Catalog # [YRB6C6CTTN](#)



Cu Splice, #6 Str(Cu)(Barrel A & B), 35 kV, 2.05" L, Tin Plating, Blue, 7 or 374 Index, For Cu to Cu.

### General

Catalog Number	YRB6C6CTTN
Color Code	Blue
Die Index	7;374
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	HYREDUCER™
UPC	781810238561

### Dimensions

Dimension - B Length inch	0.90 in
Dimension - L Length Overall mm	52 mm
Dimension - Length BB inch	0.90 in
Dimension - Length Overall inch	2.05 in
Dimension - Outside Diameter inch	0.29 in

### Conductor Related

Conductor - Copper Str Size A	6 AWG
Conductor - Copper Str Size B	6 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE211538-01](#)
- [Specifications - YRB6C6CTTN](#)
- [Specifications - BURNDY\\_YRB6C6CTTN\\_Specsheet](#)



A Hubbell brand