



# Uninsulated Reducing Splice For 6 AWG and 12 - 10 AWG

By Burndy  
Catalog # [YRV6CV10L](#)

Cu Reducer Butt Splice, W/InspWindow, Barrel A:6 Barrel C:10 (Str), 1.25" L, Tin Plated, For Aircraft Applications.



## Application

For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)

## General

Connector Type	Reducer
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	Reducing Splices
UPC	781810026373

## Dimensions

Dimension - A Outside Diameter inch	0.3 in
Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - B Outside Diameter inch	0.21 in
Dimension - Length BB inch	0.53 in
Dimension - Length Overall inch	1.25 in
Length	1.25 in

## Conductor Related

Conductor - Copper Str Size	6
Conductor - Copper Str Size B	10
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094202](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YRV6CV10L-SPEC-EN | REV 8/2023