



# YS10WAG1, Compression Splice, AL9CU, #14-10 AWG

By Burndy  
Catalog # [YS10WAG1](#)



AL Splice, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13 oxide inhibitor, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.

### Features

- Aluminum splices are dual rated to accommodate both copper and aluminum wire
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX™ Type A13 oxide inhibitor
- Color coded end caps inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel

### Application

Wire Splice

### General

Catalog Number	YS10WAG1
Connector Type	DUAL RATED
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	ALUMINUM
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	HYLINK™
UPC	781810744758
UPC 14 Digit GTIN	00781810744758

### Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - L Length Overall mm	28.45 mm
Dimension - Length Overall inch	1.12 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Strip Length inch	5/8

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - AL Str Size	14-10 AWG
Conductor - AL Str Size Range	10 AWG
Conductor - Copper Solid Size	10 AWG
Conductor - Copper Str Size	14-10 AWG
Conductor - Copper Str Size Range	14 AWG - 10 AWG
Conductor - Material	ALUMINUM / COPPER
Conductor Size	14-10 AWG
Conductor Type	CODE
Wire Size	14-10 AWG

### Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2024)
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	20
Minimum Pack Quantity	20

### Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SC081377-01](#)



A Hubbell brand